



MASTER TL-E Circular Super 80

32 W G10q Cool white Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | Voltage (Nom) | |
|------------------------------------|--------------------|-------------------------------|---|
| Cap-Base | G10q | 81 V | |
| Nominal lifetime | 15,000 hour(s) | Controls and Dimming | |
| Life to 50% Failures (Nom) | 13,000 hour(s) | Dimmable | Yes |
| Light Technical | | Mechanical and Housing | |
| Color Code | 840 [CCT of 4000K] | Bulb Shape | C-T29 |
| Luminous Flux | 2,375 lm | Net Weight (Piece) | 0.160 kg |
| Color Designation | Cool White (CW) | Approval and Application | |
| Correlated Color Temperature (Nom) | 4000 K | Mercury (Hg) Content (Nom) | 8 mg |
| Luminous Efficacy (rated) (Nom) | 74 lm/W | Energy Consumption kWh/1000 h | 35 kWh |
| Color rendering index (CRI) | 80 | Product Data | |
| Operating and Electrical | | Order product name | 32 W G10q Cool white Circular fluorescent |
| Power Consumption | 32.0 W | Full product name | 32 W G10q Cool white Circular fluorescent |
| Lamp Current (Nom) | 0.450 A | | |

MASTER TL-E Circular Super 80

| | |
|-------------------------------|-----------------|
| Full product code | 871150055968501 |
| Order code | 928026384040 |
| Material Nr. (12NC) | 928026384040 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500559685 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8711500288820 |

Dimensional drawing



| Product | D (max) | D (min) | E (min) | E (max) | I (min) | I (max) |
|--|---------|---------|----------|----------|----------|----------|
| 32 W G10q Cool white Circular fluorescent | 30.9 mm | 27.1 mm | 299.0 mm | 303.5 mm | 241.0 mm | 246.0 mm |

Photometric data



Spectral Power Distribution Colour - TL-E 32W/840 1CT/4

