



TL-E LIFEMAX

Standard Colours

40 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.

Product data

| General Information | |
|----------------------------|----------------|
| Cap-Base | G10q |
| Nominal lifetime | 8,000 hour(s) |
| Life to 50% Failures (Nom) | 13,000 hour(s) |

| Light Technical | |
|------------------------------------|---------------|
| Color Code | 54-765 |
| Luminous Flux | 2,500 lm |
| Color Designation | Cool Daylight |
| Correlated Color Temperature (Nom) | 6200 K |
| Luminous Efficacy (rated) (Nom) | 62 lm/W |
| Color rendering index (CRI) | 72 |

| Operating and Electrical | |
|--------------------------|---------|
| Power Consumption | 40.0 W |
| Lamp Current (Nom) | 0.420 A |
| Voltage (Nom) | 110 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |


| Mechanical and Housing | |
|------------------------|----------|
| Bulb Shape | C-T29 |
| Net Weight (Piece) | 0.250 kg |

| Approval and Application | |
|----------------------------|------|
| Mercury (Hg) Content (Nom) | 9 mg |

| Product Data | |
|---------------------------------|--|
| Order product name | 40 W G10q Cool daylight Circular fluorescent |
| Full product name | 40 W G10q Cool daylight Circular fluorescent |
| Full product code | 871150055991301 |
| Order code | 928027405436 |
| Material Nr. (12NC) | 928027405436 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500559913 |
| Numerator - Packs per outer box | 20 |
| EAN/UPC - Case | 8711500284501 |


TL-E LIFEMAX Standard Colours

Dimensional drawing



| Product | D (max) | D (min) | E (min) | E (max) | I (min) | I (max) |
|--|---------|---------|----------|----------|----------|----------|
| 40 W G10q Cool daylight Circular fluorescent | 30.9 mm | 27.1 mm | 393.7 mm | 406.4 mm | 341.0 mm | 347.7 mm |

Photometric data



Spectral Power Distribution Colour - TL-E 40W/54-765 1CT/20

