



TL-E 80

40 W G10q Cool daylight Circular fluorescent

Fluorescent lamps with a circular tube having a diameter of 26 mm


Product data

General Information	
Cap-Base	G10q
Nominal lifetime	8,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	3,070 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	78 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	40.0 W
Lamp Current (Nom)	0.420 A
Voltage (Nom)	110 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.240 kg
Approval and Application	
Mercury (Hg) Content (Nom)	8 mg
Energy Consumption kWh/1000 h	44 kWh
Product Data	
Order product name	40 W G10q Cool daylight Circular fluorescent
Full product name	40 W G10q Cool daylight Circular fluorescent
Full product code	871150028601700
Order code	928027486574
Material Nr. (12NC)	928027486574
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500286017
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900813623

TL-E 80

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
40 W G10q Cool daylight Circular fluorescent	30.9 mm	27.1 mm	393.7 mm	406.4 mm	341.0 mm	347.7 mm

