



# Circline

## 32W T9 Soft White Circline Fluorescent

T9 4-Pin Circular Fluorescent Lamps.

### Product data

General Information	
Cap-Base	G10q
Life to 50% Failures (Nom)	13,000 hour(s)

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,900 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	85
Number of light sources	1

Operating and Electrical	
Power Consumption	32 W
Lamp Current (Nom)	0.43 A
Voltage (Nom)	84 V

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.180 kg

Product Data	
Order product name	32W T9 Soft White Circline Fluorescent
Full product name	32W T9 Soft White Circline Fluorescent
Order code	928028683035
Material Nr. (12NC)	928028683035
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677391225
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677391220

# Circline

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32W T9 Soft White	31.0 mm	26.2 mm	292.1 mm	304.8 mm	239.5 mm	246.1 mm
Circline Fluorescent						

