



TL-X XL



TL-X XL 40W/33-640 SLV/25

The TL-X XL lamp (tube diameter 38 mm) has an extended lifetime and is fitted with an internal ignition strip for electromagnetic starterless operation or high-frequency non-preheat operation. In combination with a special lampholder, all possible sparking effects during ignition are eliminated. This lamp is used in flameproof and increased-safety luminaires for both indoor and outdoor applications, such as the (petro-)chemical industry, offshore, mines and any location where traces of explosive gases may be found.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	FA6	Power Consumption	40.0 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.430 A
Life to 50% Failures (Nom)	26,000 hour(s)	Voltage (Nom)	103 V
Light Technical		Controls and Dimming	
Color Code	33-640	Dimmable	Yes
Luminous Flux	2,300 lm	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Shape	T12
Chromaticity Coordinate X (Nom)	0.38	Net Weight (Piece)	233.000 g
Chromaticity Coordinate Y (Nom)	0.38	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Energy Efficiency Class	G
Luminous Efficacy (rated) (Nom)	58 lm/W	Mercury (Hg) Content (Max)	12 mg
Color rendering index (CRI)	60		

TL-X XL


Mercury (Hg) Content (Nom)	12.0 mg
Energy Consumption kWh/1000 h	40 kWh
EPREL Registration Number	423515
CE mark	Yes

Product Data

Order product name	TL-X XL 40W/33-640 SLV/25
Full product name	TL-X XL 40W/33-640 SLV/25
Full product code	871150026137340


Order code	928037903332
Material Nr. (12NC)	928037903332
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500261373
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500261380

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 40W/33-640 SLV/25	40.5 mm	1,183.5 mm	1,202 mm	1,198.5 mm	1,220.5 mm

Photometric data



Spectral Power Distribution Colour - TL-X XL 40W/33-640 SLV/25

