



TUV T8

TUV 30W 1SL/25-Latest

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Depreciation at Useful Lifetime	15 %
Operating and Electrical	
Power Consumption	30 W

Lamp Current (Nom)	0.365 A
Voltage (Nom)	102 V
Mechanical and Housing	
Net Weight (Piece)	134.900 g
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg


TUV T8

CE mark	Yes
UV	
UV-C Radiation at 100 hr	12.3 W
Product Data	
Order product name	TUV 30W 1SL/25-Latest
Full product name	TUV 30W 1SL/25-Latest
Full product code	871150072620940


Order code	928039504005
Material Nr. (12NC)	928039504005
Local order code	9280-395-04005
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500726209
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500638625

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 30W 1SL/25-Latest	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm



Photometric data



Spectral Power Distribution Colour - TUV 30W 1SL/25-Latest

