



Blue (/52) TL/TL-D

TL-D 18W/52

By emitting light almost entirely within the 400 to 500 nm bandwidth and peaking at 450 nm, Philips TL/TL-D color 52 lamps have no radiation from the short wave UVB. waveband. They are therefore suitable to be used in systems for applications such as Agriculture and Neonatal Jaundice Phototherapy

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take them to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

| General Information | | Controls and Dimming | |
|---------------------------------|---------------------------------|-------------------------------|-----------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] | Dimmable | Yes |
| Life to 50% Failures (Nom) | 13,000 hour(s) | | |
| Useful Life (Nom) | 2,000 hour(s) | | |
| Light Technical | | Mechanical and Housing | |
| Color Code | 52 | Bulb Shape | T26 |
| Luminous Flux | 395 lm | Net Weight (Piece) | 71.000 g |
| Chromaticity Coordinate X (Nom) | 157 | | |
| Chromaticity Coordinate Y (Nom) | 75 | | |
| Operating and Electrical | | Approval and Application | |
| Power Consumption | 18 W | Mercury (Hg) Content (Nom) | 13.0 mg |
| Lamp Current (Nom) | 0.36 A | | |
| Voltage (Nom) | 59 V | | |
| | | Product Data | |
| | | Order product name | TL-D 18W/52 |
| | | Full product name | TL-D 18W/52 |
| | | Full product code | 872790083485700 |
| | | Order code | 928048005211 |
| | | Material Nr. (12NC) | 928048005211 |
| | | Numerator - Quantity Per Pack | 1 |
| | | EAN/UPC - Product/Case | 8727900834857 |

Blue (/52) TL/TL-D

| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8727900834864 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|-------------|---------|----------|----------|----------|---------|
| TL-D 18W/52 | 28 mm | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm |

