Blue (/52) TL/TL-D

TL-D 18W/52

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Useful Life (Nom)	2,000 hour(s)

Light Technical	
Color Code	52
Luminous Flux	395 lm
Chromaticity Coordinate X (Nom)	157
Chromaticity Coordinate Y (Nom)	75

Operating and Electrical	
Power Consumption	18 W
Lamp Current (Nom)	0.36 A
Voltage (Nom)	59 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T26
Net Weight (Piece)	71.000 g

Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg

Product Data	
Order product name	TL-D 18W/52
Full product name	TL-D 18W/52
Full product code	872790083485700
Order code	928048005211
Material Nr. (12NC)	928048005211
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900834857
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900834864

Blue (/52) TL/TL-D

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/52	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.