



# Blue (/52) TL/TL-D

## TL-D 18W/52

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	13,000 hour(s)		
Useful Life (Nom)	2,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	52	Bulb Shape	T26
Luminous Flux	395 lm	Net Weight (Piece)	71.000 g
Chromaticity Coordinate X (Nom)	157		
Chromaticity Coordinate Y (Nom)	75		
Operating and Electrical		Approval and Application	
Power Consumption	18 W	Mercury (Hg) Content (Nom)	13.0 mg
Lamp Current (Nom)	0.36 A		
Voltage (Nom)	59 V		
Product Data			
Order product name	TL-D 18W/52		
Full product name	TL-D 18W/52		
Full product code	872790083485700		
Order code	928048005211		
Material Nr. (12NC)	928048005211		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8727900834857		

## Blue (/52) TL/TL-D

Numerator - Packs per outer box	25
EAN/UPC - Case	8727900834864

### Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/52	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

