



TL-D Snow White

TL-D 36W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high color temperature of the Snow White range creates very cool ambiances, making the lamp especially suitable in very hot and dry climate conditions.

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T8
Life to 50% Failures (Nom)	13,000 hour(s)	Net Weight (Piece)	135.000 g
Light Technical		Approval and Application	
Luminous Flux	2,370 lm	Mercury (Hg) Content (Nom)	5.0 mg
Color Designation	Extreme Cool Daylight	Energy Consumption kWh/1000 h	43 kWh
Chromaticity Coordinate X (Nom)	264	Product Data	
Chromaticity Coordinate Y (Nom)	280	Order product name	TL-D 36W Snow White 1SL/25
Correlated Color Temperature (Nom)	12000 K	Full product name	TL-D 36W Snow White 1SL/25
Color rendering index (CRI)	75	Full product code	871150089352940
Operating and Electrical		Order code	89352940
Power Consumption	36 W	Material Nr. (12NC)	928048545015
Lamp Current (Nom)	440 mA	Numerator - Quantity Per Pack	1
Voltage (Nom)	103 V	EAN/UPC - Product/Case	8711500893529
		Numerator - Packs per outer box	25
		EAN/UPC - Case	8711500893536

TL-D Snow White

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W Snow White 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

