



TUV T8

TUV 36W SLV/6

TUV T8 lamps are double-ended UV-C 253.7 nm emitting lamps. TUV T8 lamps offer almost constant UV-C output over their complete lifetime. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Useful Life (Nom)	9,000 hour(s)

Light Technical	
Depreciation at Useful Lifetime	15 %

Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.44 A
Voltage (Nom)	103 V

Mechanical and Housing	
Net Weight (Piece)	135.000 g

Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
CE mark	Yes


UV	
UV-C Radiation at 100 hr	16.4 W

Product Data	
Order product name	TUV 36W SLV/6
Full product name	TUV 36W SLV/6
Full product code	871150061854210
Order code	928048604003
Material Nr. (12NC)	928048604003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500618542

TUV T8


Numerator - Packs per outer box	6
EAN/UPC - Case	8711500618559

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 36W SLV/6	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TUV 36W SLV/6

