



TL-D Colored

TL-D Colored 58W Green 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	170	Bulb Shape	T8
Luminous Flux	6,750 lm	Net Weight (Piece)	167.000 g
Color Designation	Green (G)		
Operating and Electrical		Approval and Application	
Power Consumption	58.5 W	Mercury (Hg) Content (Nom)	1.7 mg
Lamp Current (Nom)	0.670 A	Energy Consumption kWh/1000 h	67 kWh
Voltage (Nom)	111 V	CE mark	Yes
Product Data			
Order product name	TL-D Colored 58W Green 1SL/25		
Full product name	TL-D Colored 58W Green 1SL/25		
Full product code	871150095449740		

TL-D Colored

Order code	928049001705
Material Nr. (12NC)	928049001705
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500954497

Numerator - Packs per outer box	25
EAN/UPC - Case	8711500954503

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 58W Green 1SL/25	28.0 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

