



TUV T8

TUV 55W HO 1SL/6

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Net Weight (Piece)	134.900 g
Useful Life (Nom)	9,000 h		
Light Technical		Approval and Application	
Depreciation at Useful Lifetime	15 %	Mercury (Hg) Content (Nom)	2.0 mg
		CE mark	Yes
Operating and Electrical		UV	
Power Consumption	54 W	UV-C Radiation at 100 hr	19.7 W
Lamp Current (Nom)	0.765 A		
Voltage (Nom)	86 V		
Product Data			
Order product name	TUV 55W HO 1SL/6		
Full product name	TUV 55W HO 1SL/6		
Full product code	871150061866510		


TUV T8

Local code description	TUV55WHO
Order code	928049504003
Material Nr. (12NC)	928049504003
Local order code	TUV55WHO
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711500618665
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500618672

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 55W HO 1SL/6	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm



Photometric data



Spectral Power Distribution Colour - TUV 55W HO 1SL/6

