



MASTER CityWhite CDO-TT

MASTER CityWh CDO-TT Plus 50W/828 E27

Ceramic metal halide lamp with clear tubular outer bulb shape, used in outdoor offering pleasant white light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electromagnetic control gear or electronic gear suitable to drive CDO lamps (e.g. HID-PV Xt CDO)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Warm restart time can be up to 15 minutes; T15 ignitors therefore advised
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	E27		104 lm/W
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	84
Flux measurement reference	Sphere	Arc Length O (Nom)	5.25 mm
Life to 50% Failures (Nom)	21,000 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	53.0 W
Color Code	828 [CCT of 2800K]	Voltage (Nom)	83 V
Luminous Flux	5,500 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Chromaticity Coordinate X (Nom)	0.447	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	0.4	Bulb Finish	Clear
Correlated Color Temperature (Nom)	2800 K		

MASTER CityWhite CDO-TT

Bulb Shape	T31
Net Weight (Piece)	0.060 kg

Approval and Application


Energy Efficiency Class	F
Mercury (Hg) Content (Max)	5.4 mg
Mercury (Hg) Content (Nom)	5.4 mg
Energy Consumption kWh/1000 h	53 kWh
EPREL Registration Number	473330
CE mark	Yes

Product Data

Order product name	MASTER CityWh CDO-TT Plus 50W/828 E27
--------------------	---------------------------------------


Full product name	MASTER CityWh CDO-TT Plus 50W/828 E27
Full product code	871829118561100
Order code	928082419235
Material Nr. (12NC)	928082419235
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291185611
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291185628

Dimensional drawing




Product	D (max)	O	L	C (max)
MASTER CityWh CDO-TT Plus 50W/828 E27	36 mm	5.25 mm	102 mm	156 mm

Photometric data





Light Distribution Diagram - MASTER CityWh CDO-TT Plus 50W/828 E27



Spectral Power Distribution Colour - MASTER CityWh CDO-TT Plus 50W/828 E27

MASTER CityWhite CDO-TT

Lifetime



LDLE_CDO-TT_0004-Life expectancy diagram

Lumen Maintenance Diagram - MASTER CityWh CDO-TT Plus 50W/828 E27

