



# MASTERCoulour CDM-T



## MASTERC CDM-T 70W/942 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G12
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	12,000 hour(s)
Light Technical	
Color Code	942 [CCT of 4200K]
Luminous Flux	6,200 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.371
Chromaticity Coordinate Y (Nom)	0.366
Correlated Color Temperature (Nom)	4200 K

Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	92
Arc Length O (Nom)	6 mm
Operating and Electrical	
Power Consumption	73.2 W
Voltage (Nom)	88 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

# MASTERC colour CDM-T


Bulb Shape	T19
Net Weight (Piece)	0.029 kg
<b>Approval and Application</b>	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	6.1 mg
Mercury (Hg) Content (Nom)	6.1 mg
Energy Consumption kWh/1000 h	74 kWh
EPREL Registration Number	473337
CE mark	Yes

## Product Data

Order product name	MASTERC CDM-T 70W/942 G12 1CT/12
--------------------	----------------------------------


Full product name	MASTERC CDM-T 70W/942 G12 1CT/12
Full product code	871150019927015
Order code	928084505131
Material Nr. (12NC)	928084505131
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500199270
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500199287

## Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 70W/942 G12 1CT/12	20 mm	0.75 inch	6 mm	55 mm	57 mm	56 mm	103 mm

## Photometric data





Spectral Power Distribution Colour - MASTERC CDM-T 70W/942 G12 1CT/12



Light Distribution Diagram - MASTERC CDM-T 70W/942 G12 1CT/12

# MASTERC colour CDM-T

## Lifetime



LDLE\_CDM-T\_70W\_942-Life expectancy diagram

Lumen Maintenance Diagram - MASTERC CDM-T 70W/942 G12 1CT/12

