



MASTERColour CDM-T 陶瓷複金屬燈

MASTERC CDM-T 150W/942 G12 1CT

精巧、高效率單端型放電式反射燈具系列，光色歷久如新，光線清晰明亮

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊		演色性指數 (CRI)	
燈座基底	G12		96
操作位置	UNIVERSAL [任何或通用 (U)]	電弧長 O (標稱)	8 mm
通量測量參考	Sphere	運轉與電力	
壽命 (故障率 50%) (標稱)	12,000 h	耗電量	150.1 W
照明技術		電壓 (標稱)	90 V
色碼	942 [CCT of 4200K]	控制與調光	
光通量	12,100 lm	可調光	否
色彩名稱	冷白光 (CW)	機械與外罩	
色度坐標 X (標稱)	0.371	燈泡表層	透明
色度坐標 Y (Nom)	0.366	燈泡形狀	T19
相關色溫 (標稱)	4200 K		
光效 (額定) (標準)	82 lm/W		

MASTERC colour CDM-T 陶瓷複金屬燈


淨重 (個)	0.033 kg
認證與應用	
節能等級	G
汞 (Hg) 含量 (最大)	10.4 mg
汞 (Hg) 含量 (標稱)	10.4 mg
能源消耗 kWh/1000 h	151 kWh
EPREL 註冊碼	473338
CE 標誌	是

產品資料

下訂產品名稱	MASTERC CDM-T 150W/942 G12 ICT
--------	--------------------------------


完整產品名稱	MASTERC CDM-T 150W/942 G12 ICT
完整產品代碼	871150020005115
訂單代碼	928084605131
材質 Nr. (12NC)	928084605131
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500200051
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500200068

二维绘图




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/942 G12 ICT	20 mm	0.75 in	8 mm	55 mm	57 mm	56 mm	110 mm

光度数据





Spectral Power Distribution Colour - MASTERC CDM-T 150W/942 G12 ICT



Light Distribution Diagram - MASTERC CDM-T 150W/942 G12 ICT

MASTERC colour CDM-T 陶瓷複金屬燈

壽命



LDLE_CDM-T_150W_942-Life expectancy diagram

Lumen Maintenance Diagram - MASTERC CDM-T 150W/942 G12 1CT

