

PHILIPS

Lighting



# MASTERColour CDM-TC 陶瓷複金屬燈

## MASTERC CDM-TC 35W/830 G8.5 1CT/12

超精巧、高效率單端型放電燈，光色歷久如新，光線清晰明亮

### 安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

一般資訊	
燈座基底	G8.5
操作位置	UNIVERSAL [任何或通用 (U)]
壽命 (故障率 50%) (標稱)	12,000 h

照明技術	
色碼	830 [CCT of 3000K]
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.432
色度坐標 Y (Nom)	0.394
相關色溫 (標稱)	3000 K
光效 (額定) (標準)	79 lm/W
演色性指數 (CRI)	81
電弧長 O (標稱)	5 mm

運轉與電力	
耗電量	39.1 W
電壓 (標稱)	88 V

控制與調光	
可調光	否

機械與外罩	
燈泡表層	透明
燈泡材質	抗 UV 石英
燈泡形狀	T14
淨重 (個)	10.000 g


認證與應用	
汞 (Hg) 含量 (標稱)	3.1 mg

# MASTERC colour CDM-TC 陶瓷複金屬燈

能源消耗 kWh/1000 h	43 kWh
<b>產品資料</b>	
下訂產品名稱	MASTERC CDM-TC 35W/830 G8.5 1CT/12
完整產品名稱	MASTERC CDM-TC 35W/830 G8.5 1CT/12
完整產品代碼	871869648459300
訂單代碼	928085205129



材質 Nr. (12NC)	928085205129
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718696484593
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8718696484609

## 二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 35W/830 G8.5 1CT/12	15 mm	0.5 in	5 mm	51 mm	53 mm	52 mm	85 mm

## 光度数据





Light Distribution Diagram - MASTERC CDM-TC 35W/830 G8.5 1CT/12

Spectral Power Distribution Colour - MASTERC CDM-TC 35W/830 G8.5 1CT/12

# MASTERC colour CDM-TC 陶瓷複金屬燈

## 壽命



Lumen Maintenance Diagram - MASTERC CDM-TC 35W/830 G8.5 1CT/12

LDLE\_CDM-TC\_0001-Life expectancy diagram

