



# CDM

## CDM-SA/R 150W/942 UNP/1

Compact reflector discharge lamps with quartz outer bulb

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information	
Cap-Base	Ceramic Cap-Cable (C)
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Color Code	942 [CCT of 4200K]
Luminous Flux (Min)	2,295 lm
Luminous Flux	2,550 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	16.1 lm/W
Color rendering index (CRI)	96
Operating and Electrical	
Power Consumption	158.0 W
Lamp Current (Nom)	1.76 A
Voltage (Nom)	106 V

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Net Weight (Piece)	192.000 g
Product Data	
Order product name	CDM-SA/R 150W/942 UNP/1
Full product name	CDM-SA/R 150W/942 UNP/1
Full product code	871951441092300
Order code	928086805305
Material Nr. (12NC)	928086805305
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514410923
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514410930

# CDM

## Dimensional drawing



Product	D (max)	X	C (max)
CDM-SA/R 150W/942 UNP/1	95.3 mm	280 mm	106 mm

