

PHILIPS

Lighting



MASTER MHN-SA 複金屬燈

MASTER MHN-SA 1800W/956 230V XW UNP/1

雙封式袖珍型石英複金屬燈

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般資訊		電壓 (標稱)		120 V	
燈座基底	X830R	控制與調光			
操作位置	P15 [平行 +/-15D 或水平 (HOR)]	可調光		否	
壽命 (故障率 50%) (標稱)	5,000 h	機械與外罩			
照明技術		燈泡表層		透明	
色碼	956 [CCT of 5600K]	燈泡形狀		TD40	
色彩名稱	日光	淨重 (個)		110.000 g	
色度坐標 X (標稱)	330	認證與應用			
色度坐標 Y (Nom)	339	汞 (Hg) 含量 (標稱)		87 mg	
相關色溫 (標稱)	5600 K	能源消耗 kWh/1000 h		1,980 kWh	
光效 (額定) (標準)	86 lm/W	CE 標誌		是	
演色性指數 (CRI)	86	產品資料			
電弧長 O (標稱)	25 mm	下訂產品名稱		MASTER MHN-SA 1800W/956 230V XW UNP/1	
運轉與電力					
耗電量	1,800.0 W				

MASTER MHN-SA 複金屬燈

完整產品名稱	MASTER MHN-SA 1800W/956 230V XW UNP/1
完整產品代碼	871150020106500
訂單代碼	928099205130
材質 Nr. (12NC)	928099205130
分子 - 每個包裝的數量	1


EAN/UPC - 產品/案例	8718291548294
分子 - 每一外盒包裝	1
EAN/UPC - 箱	8711500201065

二维绘图




Product	D (max)	O	X	A	C (max)
MASTER MHN-SA 1800W/956 230V XW UNP/1	41 mm	25 mm	25 mm	318 mm	369 mm

光度数据




Spectral Power Distribution Colour - MASTER MHN-SA 1800W/956 230V XW UNP/1

壽命



MHN SA 1800W 956 Life Expectancy Diagram



Lumen Maintenance Diagram - MASTER MHN-SA 1800W/956 230V XW UNP/1

MASTER MHN-SA 複金屬燈

