



# MASTER SON-T PIA Plus 高壓鈉燈

## MST SON-T PIA Plus 400W E E40 1SL/12

本產品為高壓鈉燈管，採用透明外管，具有高輸出、品質穩定、以及使用壽命長等特色

### 安全提示

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

一般資訊	
燈座基底	E40
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	36,000 h
照明技術	
色碼	220 [CCT of 2000K]
光通量	55,900 lm
色度坐標 X (標稱)	0.535
色度坐標 Y (Nom)	0.42
相關色溫 (標稱)	2000 K
光效 (額定) (標準)	137 lm/W
演色性指數 (CRI)	-
電弧長 O (標稱)	83 mm
運轉與電力	
耗電量	408.0 W

電壓 (標稱)	105 V
控制與調光	
可調光	是
機械與外罩	
燈泡表層	透明
燈泡形狀	T46
淨重 (個)	0.180 kg
認證與應用	
節能等級	E
汞 (Hg) 含量 (最大)	19.6 mg
汞 (Hg) 含量 (標稱)	20 mg
能源消耗 kWh/1000 h	408 kWh
EPREL 註冊碼	473369
CE 標誌	是


# MASTER SON-T PIA Plus 高壓鈉燈

## 產品資料

下訂產品名稱	MST SON-T PIA Plus 400W E E40 1SL/12
完整產品名稱	MST SON-T PIA Plus 400W E E40 1SL/12
完整產品代碼	871150017988315
訂單代碼	928144809227
材質 Nr. (12NC)	928144809227


分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500179883
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500182951

## 二维绘图




Product	D (max)	O	L	C (max)
MST SON-T PIA Plus 400W E E40 1SL/12	48 mm	83 mm	175 mm	279 mm

## 光度数据




Light Distribution Diagram - MST SON-T PIA Plus 400W E E40 1SL/12




Spectral Power Distribution Colour - MST SON-T PIA Plus 400W E E40 1SL/12

## 壽命



Lumen Maintenance Diagram - MST SON-T PIA Plus 400W E E40 1SL/12



SON(-)T PIA Plus 150W 250W 400W Life Expectancy Diagram

## MASTER SON-T PIA Plus 高壓鈉燈

