



HORTI

MASTER GreenPower Xtra 1000W EL/5X6CT

High Pressure Sodium lamp with clear outer bulb, optimized growthlight output and maintenance

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	K12x30s
Operating Position	P [Parallel or Horizontal(HOR)]
Light Technical	
Color Code	220 [CCT of 2000K]
Chromaticity Coordinate X (Nom)	0.537
Chromaticity Coordinate Y (Nom)	0.427
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	155 lm/W
Color rendering index (CRI)	33
Arc Length O (Nom)	147 mm
Operating and Electrical	
Power Consumption	1,020.0 W
Voltage (Nom)	220 V
Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T40
Net Weight (Piece)	108.000 g
Approval and Application	
Mercury (Hg) Content (Nom)	35 mg
Energy Consumption kWh/1000 h	1,020 kWh
Product Data	
Order product name	MASTER GreenPower Xtra 1000W EL/5X6CT
Full product name	MASTER GreenPower Xtra 1000W EL/5X6CT
Full product code	871869682951600
Order code	928152419216
Material Nr. (12NC)	928152419216
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696829516
Numerator - Packs per outer box	30
EAN/UPC - Case	8718696829530

Dimensional drawing



Product	D (max)	Ø	C (max)	A
MASTER GreenPower Xtra 1000W EL/5X6CT	33.5 mm	147 mm	394 mm	325 mm

Photometric data



Spectral Power Distribution Colour - MASTER GreenPower Xtra 1000W EL/5X6CT

