PHILIPS

Lighting

MASTER SDW-TG Mini 迷你高強度放電燈

MST SDW-TG Mini 100W/825 GX12-1 1CT/12

高效率放電燈暖色系列，主要用於 MASTERColour CDM-T 燈管專用的小型開放式燈具

安全提示

- Use only with dedicated Philips control gear
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	GX12-1
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	10,000 h

照明技術	
色碼	825 [CCT of 2500K]
光通量	5,300 lm
色彩名稱	黃金白色
色度坐標 X (標稱)	0.478
色度坐標 Y (Nom)	0.415
相關色溫 (標稱)	2500 K
光效 (額定) (標準)	52 lm/W
演色性指數 (CRI)	82
電弧長 O (標稱)	18 mm

運轉與電力	
耗電量	102.0 W
電壓 (標稱)	91 V

控制與調光	
可調光	否

機械與外罩	
燈泡表層	透明
燈泡材質	玻璃
燈泡形狀	T19
淨重 (個)	0.030 kg

認證與應用	
節能等級	G
汞 (Hg) 含量 (最大)	15.2 mg
汞 (Hg) 含量 (標稱)	15.2 mg
能源消耗 kWh/1000 h	102 kWh

MASTER SDW-TG Mini 迷你高強度放電燈

EPREL 註冊碼	473402

材質 Nr. (12NC)	928158905131
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500202338
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500202345

產品資料	
下訂產品名稱	MST SDW-TG Mini 100W/825 GX12-1 1CT/12
完整產品名稱	MST SDW-TG Mini 100W/825 GX12-1 1CT/12
完整產品代碼	871150020233815
訂單代碼	928158905131

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MST SDW-TG Mini 100W/825 GX12-1 1CT/12	20 mm	0.75 in	18 mm	54.5 mm	57.5 mm	56 mm	110 mm

光度数据



Spectral Power Distribution Colour - MST SDW-TG Mini 100W/825 GX12-1 1CT/12

壽命



LDLE_SDW-TG_100W_825-Life expectancy diagram



Lumen Maintenance Diagram - MST SDW-TG Mini 100W/825 GX12-1 1CT/12

MASTER SDW-TG Mini 迷你高強度放電燈

© 2023 Signify Holding 保留一切權利。 Signify 不對本協議所含括資訊之準確性及完整性提供任何聲明或保證，對以此訊息為依據採取的任何行動亦概不負責。 除非 Signify 同意，本文件提及之資訊並非任何商業合約，亦不構成任何報價或合約任一部分。
Philips 與 Philips Shield Emblem 均屬 Koninklijke Philips N.V 註冊商標。

www.lighting.philips.com
2023, 四月 16 - 要更改的数据主题