

PHILIPS

Lighting



MASTER SDW-TG Mini 迷你高強度放電燈

MST SDW-TG Mini 50W/825 GX12-1 1CT/12

高效率放電燈暖色系列，主要用於 MASTERColour CDM-T 燈管專用的小型開放式燈具

安全提示

- Use only with dedicated Philips control gear
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	GX12-1
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	10,000 h

照明技術	
色碼	825 [CCT of 2500K]
光通量	2,400 lm
色彩名稱	黃金白色
色度坐標 X (標稱)	0.478
色度坐標 Y (Nom)	0.415
相關色溫 (標稱)	2500 K
光效 (額定) (標準)	44 lm/W
演色性指數 (CRI)	81
電弧長 O (標稱)	14 mm

運轉與電力	
耗電量	54.0 W
電壓 (標稱)	85 V

控制與調光	
可調光	否

機械與外罩	
燈泡表層	透明
燈泡材質	玻璃
燈泡形狀	T19
淨重 (個)	0.034 kg


認證與應用	
節能等級	G
汞 (Hg) 含量 (最大)	5.7 mg
汞 (Hg) 含量 (標稱)	5.7 mg
能源消耗 kWh/1000 h	54 kWh

MASTER SDW-TG Mini 迷你高強度放電燈

EPREL 註冊碼	473250
產品資料	
下訂產品名稱	MST SDW-TG Mini 50W/825 GX12-1 1CT/12
完整產品名稱	MST SDW-TG Mini 50W/825 GX12-1 1CT/12
完整產品代碼	871150020323615
訂單代碼	928159905131


材質 Nr. (12NC)	928159905131
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500203236
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500203243

二维绘图




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MST SDW-TG Mini 50W/825 GX12-1 1CT/12	20 mm	0.75 in	14.5 mm	53.5 mm	56.5 mm	55 mm	103 mm

光度数据




Spectral Power Distribution Colour - MST SDW-TG Mini 50W/825 GX12-1 1CT/12

壽命



LDLE_SDW-TG_50W_825-Life expectancy diagram



Lumen Maintenance Diagram - MST SDW-TG Mini 50W/825 GX12-1 1CT/12

MASTER SDW-TG Mini 迷你高強度放電燈

