



MSR

MSR 1200/2 1CT/3

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Operating and Electrical	
Cap-Base	G22	Power Consumption	1,200 W
Operating Position	UNIVERSAL [Any or Universal (U)]	Lamp Current (Nom)	13.8 A
Life to 50% Failures (Nom)	800 hour(s)		
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	No
Luminous Flux	104,000 lm	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	302	Net Weight (Piece)	0.150 kg
Chromaticity Coordinate Y (Nom)	320	Approval and Application	
Correlated Color Temperature (Nom)	7200 K	CE mark	Yes
Luminous Efficacy (rated) (Nom)	87 lm/W	Product Data	
Color rendering index (CRI)	85	Order product name	MSR 1200/2.1CT/3
Arc Length O (Nom)	10.0 mm		

Full product name	MSR 1200/2.1CT/3
Full product code	872790091133600
Order code	91133600
Material Nr. (12NC)	928171805114
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8727900911336
Numerator - Packs per outer box	3
EAN/UPC - Case	8727900911343

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200/2.1CT/3	40 mm	10.0 mm	84 mm	86 mm	85 mm	175 mm	53 mm

Photometric data



Spectral Power Distribution Colour - MSR 1200/2.1CT/3

