



# MSR Gold™ FastFit

## MSR Gold 1200 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Color rendering index (CRI)	
Cap-Base	PGJX50		80
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	5.5 mm
Life to 50% Failures (Nom)	750 hour(s)	<b>Operating and Electrical</b>	
<b>Light Technical</b>		Power Consumption	1,200 W
Color Code	- [Not Specified]	Lamp Current (Nom)	15 A
Luminous Flux	92,000 lm	<b>Controls and Dimming</b>	
Chromaticity Coordinate X (Nom)	318	Dimmable	Yes
Chromaticity Coordinate Y (Nom)	327		
Correlated Color Temperature (Nom)	6000 K		
Luminous Efficacy (rated) (Nom)	76.5 lm/W		

# MSR Gold™ FastFit

Mechanical and Housing	
Net Weight (Piece)	0.147 kg


Approval and Application	
CE mark	Yes

Product Data	
Order product name	MSR Gold 1200 FastFit 1CT/4
Full product name	MSR Gold 1200 FastFit 1CT/4

Full product code	871829122129600
Order code	928175005115
Material Nr. (12NC)	928175005115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221296
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221302

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 1200 FastFit 1CT/4	26.1 mm	5.5 mm	64 mm	66 mm	65 mm	128 mm	50 mm

