



# MSR Gold™ MiniFastFit (DJ/Club)

## MSR Gold 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	PGJX28
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Color Code	2
Luminous Flux	22,700 lm
Chromaticity Coordinate X (Nom)	288
Chromaticity Coordinate Y (Nom)	306
Correlated Color Temperature (Nom)	9300 K
Luminous Efficacy (Rated) (Min)	64 lm/W
Luminous Efficacy (rated) (Nom)	75 lm/W

Color rendering index (CRI)	78
Arc Length O (Nom)	5.0 mm
Operating and Electrical	
Power Consumption	300 W
Lamp Current (Nom)	3.75 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	0.062 kg

## MSR Gold™ MiniFastFit (DJ/Club)

### Approval and Application

CE mark Yes

### Product Data

Order product name	MSR Gold 300/2 MiniFastFit 1CT/4
Full product name	MSR Gold 300/2 MiniFastFit 1CT/4
Full product code	87182912211100
Order code	928177105115

Material Nr. (12NC)	928177105115
---------------------	--------------


Numerator - Quantity Per Pack	1
-------------------------------	---

EAN/UPC - Product/Case	8718291221111
------------------------	---------------

Numerator - Packs per outer box	4
---------------------------------	---

EAN/UPC - Case	8718291221128
----------------	---------------

### Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold 300/2 MiniFastFit 1CT/4	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm

