



MSD Platinum (Touring/Stage)

MSD Platinum 14 R 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	-
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Color Code	2
Luminous Flux	12,350 lm
Chromaticity Coordinate X (Nom)	0.300
Chromaticity Coordinate Y (Nom)	0.315
Correlated Color Temperature (Nom)	7800 K
Arc Length O (Nom)	1.0 mm


Operating and Electrical	
Power Consumption	280 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	80.000 g
Product Data	
Order product name	MSD Platinum 14 R 1CT/8
Full product name	MSD Platinum 14 R 1CT/8
Full product code	871869644061200

MSD Platinum (Touring/Stage)

Order code	928196105314
Material Nr. (12NC)	928196105314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696440612


Numerator - Packs per outer box	8
EAN/UPC - Case	8718696440629

Dimensional drawing



Product	D (max)	T (max)	O	C (max)
MSD Platinum 14 R 1CT/8	51.5 mm	6.8 mm	0.95 mm	57.1 mm

Photometric data



Spectral Power Distribution Colour - MSD Platinum 14 R 1CT/8

