



# MSR Gold™ MiniFastFit (Touring/ Stage)

## MSR Gold 700/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	PGJX28	Correlated Color Temperature (Nom)	7200 K
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Efficacy (rated) (Nom)	68.5 lm/W
Life to 50% Failures (Nom)	750 hour(s)	Color rendering index (CRI)	75
		Arc Length O (Nom)	3.8 mm
Light Technical			
Color Code	2	Power Consumption	700 W
Luminous Flux (Min)	44,000 lm	Lamp Current (Nom)	10.2 A
Luminous Flux	48,000 lm		
Chromaticity Coordinate X (Nom)	300		
Chromaticity Coordinate Y (Nom)	324		

# MSR Gold™ MiniFastFit (Touring/Stage)

<b>Controls and Dimming</b>	
Dimmable	Yes
<b>Mechanical and Housing</b>	
Net Weight (Piece)	0.052 kg
<b>Approval and Application</b>	
CE mark	Yes
<b>Product Data</b>	
Order product name	MSR Gold 700/2 MiniFastFit 1CT/4


Full product name	MSR Gold 700/2 MiniFastFit 1CT/4
Full product code	871829122117300
Order code	928199905115
Material Nr. (12NC)	928199905115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221173
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221180

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 700/2 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

## Photometric data



Spectral Power Distribution Colour - MSR Gold 700/2 MiniFastFit 1CT/4

## MSR Gold™ MiniFastFit (Touring/Stage)

