



Starters for tanning lamps

BodyTone St 120-180W 230-240V 20x25

Range of premium-quality starters for igniting fluorescent lamps operating on electromagnetic ballasts

Warnings and Safety

- Flame-retardant components
- UV-resistant canister


Product data

Operating and Electrical	
Power Consumption	120 180 W
Voltage (Nom)	230-240 V
Mechanical and Housing	
Housing Color	Black
Net Weight (Piece)	7.000 g
Product Data	
Order product name	BodyTone St 120-180W 230-240V 20x25

Full product name	BodyTone St 120-180W 230-240V 20x25
Full product code	871150090348826
Order code	928391930303
Material Nr. (12NC)	928391930303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500903488
Numerator - Packs per outer box	500
EAN/UPC - Case	8711500903501

Starters for tanning lamps

Dimensional drawing



Product	C (max)	E (max)
BodyTone St 120-180W 230-240V 20x25	40.3 mm	21.5 mm

