



Safety Starters

S10 4-65W SIN 220-240V BL LIS/12X25


Range of Blue glow switch starters for igniting fluorescent lamps with electromagnetic ballast. 2-pin igniter in plastic (flame-retardant polycarbonate) canister and radio-interference suppression capacitor

Product data

Operating and Electrical	
Power Consumption	4 65 W
Voltage (Nom)	220-240 V
Mechanical and Housing	
Housing Color	Blue
Net Weight (Piece)	7.000 g
Product Data	
Order product name	S10 4-65W SIN 220-240V BL LIS/12X25

Full product name	S10 4-65W SIN 220-240V BL LIS/12X25
Full product code	872790088649800
Order code	928392110114
Material Nr. (12NC)	928392110114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900886498
Numerator - Packs per outer box	300
EAN/UPC - Case	8727900886511

Dimensional drawing



Product	C (max)	E (max)
S10 4-65W SIN 220-240V BL LIS/12X25	40.3 mm	21.5 mm