



Safety Starters

S10 4-65W SIN 220-240V BL LAT/20X25CT


Range of Blue glow switch starters for igniting fluorescent lamps with electromagnetic ballast. 2-pin igniter in plastic (flame-retardant polycarbonate) canister and radio-interference suppression capacitor

Product data

Operating and Electrical	
Power Consumption	4 65 W
Voltage (Nom)	220-240 V
Mechanical and Housing	
Housing Color	Blue
Net Weight (Piece)	7.000 g
Product Data	
Order product name	S10 4-65W SIN 220-240V BL LAT/20X25CT

Full product name	S10 4-65W SIN 220-240V BL LAT/20X25CT
Full product code	871150090298626
Order code	928392110175
Material Nr. (12NC)	928392110175
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500902986
Numerator - Packs per outer box	500
EAN/UPC - Case	8711500903006

Dimensional drawing



Product	C (max)	E (max)
S10 4-65W SIN 220-240V BL LAT/20X25CT	40.3 mm	21.5 mm