



# MH-NaSc

## MH 100W/640 E27 CL 1SL/24

Sodium Scandium Metal Halide Lamps consisting of a gasfilled glass bulb, which alternatively are clear or internal coated, and a quartz discharge tube (DT).


### Product data

General Information	
Cap-Base	E27
Operating Position	H [Hanging or Base Up (BU)]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	640 [CCT of 4000K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	375
Chromaticity Coordinate Y (Nom)	385
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	92 lm/W
Color rendering index (CRI)	65
Operating and Electrical	
Power Consumption	105 W
Voltage (Nom)	100 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ED55
Net Weight (Piece)	0.072 kg
Approval and Application	
Mercury (Hg) Content (Nom)	10.2 mg
Energy Consumption kWh/1000 h	110 kWh
Product Data	
Order product name	MH 100W/640 E27 CL 1SL/24
Full product name	MH 100W/640 E27 CL 1SL/24
Full product code	692234199956700
Order code	928484500093
Material Nr. (12NC)	928484500093
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341999567
Numerator - Packs per outer box	24
EAN/UPC - Case	6922341993176



# MH-NaSc

## Dimensional drawing



Product	D (max)	L (min)	C (max)
MH 100W/640 E27 CL 1SL/24	56 mm	83 mm	141 mm

## Lifetime



LDLE\_MH\_0009-Life expectancy diagram

Lumen Maintenance Diagram - MH 100W/640 E27 CL 1SL/24

