



# SON-T

## SON-T 1000W E E40 1SL/4

High Pressure Sodium lamp with clear tubular outer bulb

### Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	E40
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	20,000 h

Light Technical	
Color Code	220 [CCT of 2000K]
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	-
Arc Length O (Nom)	145 mm

Operating and Electrical	
Power Consumption	960.0 W
Voltage (Nom)	100 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T65
Net Weight (Piece)	0.404 kg

Approval and Application	
Mercury (Hg) Content (Nom)	22.65 mg
Energy Consumption kWh/1000 h	1,056 kWh


Product Data	
Order product name	SON-T 1000W E E40 1SL/4
Full product name	SON-T 1000W E E40 1SL/4
Full product code	871150021060945
Local code description	SONT1000WGES
Order code	928487400091
Material Nr. (12NC)	928487400091
Local order code	SONT1000WGES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500210609
Numerator - Packs per outer box	4

# SON-T

EAN/UPC - Case




8711500210616

## Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 1000W E E40 1SL/4	66 mm	145 mm	240 mm	390 mm



## Photometric data



Light Distribution Diagram - SON-T 1000W E E40 1SL/4

Spectral Power Distribution Colour - SON-T 1000W E E40 1SL/4

## Lifetime



LDLE\_SON-T\_1000W-Life expectancy diagram

Lumen Maintenance Diagram - SON-T 1000W E E40 1SL/4

SON-T

