



Pulse Start Metal Halide Standard

MS1000/BU/BT37/PS 6PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	H10 [Hanging +/-10D or Base Up (BU)]
Light Technical	
Color Code	640 [CCT of 4000K]
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.390
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	65
Operating and Electrical	
Power Consumption	1,000 W
Lamp Current (Nom)	4.1 A
Voltage (Nom)	836 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	BT37
Net Weight (Piece)	0.001 kg
Approval and Application	
Mercury (Hg) Content (Nom)	151 mg
Product Data	
Order product name	MS1000/BU/BT37/PS 6PK
Full product name	MS1000/BU/BT37/PS 6PK
Order code	928601132003
Material Nr. (12NC)	928601132003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677360191

Pulse Start Metal Halide Standard

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677360196

Dimensional drawing



Product	D	C (max)
MS1000/BU/BT37/PS 6PK		292.0 mm

