



Ceramalux ALTO

SON 250W E39 ED58 CL SL/12

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	523
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	26
Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	3.0 A
Voltage (Nom)	95 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED18
Net Weight (Piece)	167.000 g

Approval and Application	
Mercury (Hg) Content (Max)	23.5 mg

Product Data	
Order product name	SON 250W E39 ED58 CL SL/12
Full product name	SON 250W E39 ED58 CL SL/12
Order code	928601139490
Material Nr. (12NC)	928601139490
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467210
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467215

Ceramalux ALTO

Dimensional drawing

Product	D	C (max)
SON 250W E39 ED58 CL SL/12	57.2 mm	248 mm

