



Ceramalux Non-ALTO

C1000S52/ED37 6PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.


Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	517
Chromaticity Coordinate Y (Nom)	423
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	108 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	1,003 W
Lamp Current (Nom)	4.7 A
Voltage (Nom)	225 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED37
Net Weight (Piece)	0.001 kg
Approval and Application	
Mercury (Hg) Content (Max)	55.2 mg
Product Data	
Order product name	C1000S52/ED37 6PK
Full product name	C1000S52/ED37 6PK
Order code	928601140701
Material Nr. (12NC)	928601140701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677323868
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677323863

Ceramalux Non-ALTO

Dimensional drawing



Product	D	C (max)
C1000S52/ED37 6PK	120 mm	289 mm

