



Ceramalux Instant Restrike

C100S54/2 1/12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]

Light Technical	
Chromaticity Coordinate X (Nom)	520
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	84 lm/W
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	21

Operating and Electrical	
Power Consumption	100.4 W
Lamp Current (Nom)	2.1 A
Voltage (Nom)	55 V

Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2
Net Weight (Piece)	0.001 kg

Approval and Application	
Mercury (Hg) Content (Max)	44.4 mg

Product Data	
Order product name	C100S54/2 1/12PK
Full product name	C100S54/2 1/12PK
Order code	928601145701
Material Nr. (12NC)	928601145701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677265601
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677265606

Ceramalux Instant Restrike

Dimensional drawing

Product	D	C (max)
C100S54/2 1/12PK	2.938 inch	7.75 inch

