



Pulse Start Metal Halide Standard

MS175/BU/PS 12PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


| General Information | | Voltage (Nom) | |
|---------------------------------|--------------------------------------|----------------------------|------------------|
| Cap-Base | E39 [Single Contact Mogul Screw] | 132 V | |
| Operating Position | H15 [Hanging +/-15D or Base Up (BU)] | Mechanical and Housing | |
| Life to 50% Failures (Nom) | 15,000 hour(s) | Bulb Finish | Clear |
| Light Technical | | Bulb Material | Hard Glass |
| Color Code | 635 [CCT of 3500K] | Bulb Shape | ED28 |
| Color Designation | White (WH) | Net Weight (Piece) | 0.001 kg |
| Chromaticity Coordinate X (Nom) | 395 | Approval and Application | |
| Chromaticity Coordinate Y (Nom) | 390 | Mercury (Hg) Content (Nom) | 23.5 mg |
| Luminous Efficacy (Rated) (Min) | 82.3 lm/W | Product Data | |
| Luminous Efficacy (rated) (Nom) | 91 lm/W | Order product name | MS175/BU/PS 12PK |
| Color rendering index (CRI) | 62 | Full product name | MS175/BU/PS 12PK |
| Operating and Electrical | | Order code | 928601152103 |
| Lamp Current (Nom) | 1.5 A | Material Nr. (12NC) | 928601152103 |

Pulse Start Metal Halide Standard

| | |
|---------------------------------|--------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677276621 |
| Numerator - Packs per outer box | 12 |

| | |
|----------------|----------------|
| EAN/UPC - Case | 50046677276626 |
|----------------|----------------|

Dimensional drawing



| Product | D | C (max) |
|------------------|----------|------------|
| MS175/BU/PS 12PK | 3.5 inch | 8.313 inch |

