



Ceramalux ALTO Non-Cycling

C250S50/ALTO NC HPS 1/12PK

Philips Ceramalux High Pressure Sodium Non-Cycling Lamps are a better value than standard high pressure sodium lamps, with longer life and reduced maintenance cost.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® Non-Cycling

Light Technical	
Chromaticity Coordinate X (Nom)	0.523
Chromaticity Coordinate Y (Nom)	0.415
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	21

Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	1.8 A
Voltage (Nom)	100 V

Mechanical and Housing	
Bulb Finish	Clear


Bulb Material	Hard Glass
Bulb Shape	ED18
Net Weight (Piece)	160.000 g

Approval and Application	
Mercury (Hg) Content (Nom)	3.36 mg

Product Data	
Order product name	C250S50/ALTO NC HPS 1/12PK
Full product name	C250S50/ALTO NC HPS 1/12PK
Order code	928601156190
Material Nr. (12NC)	928601156190
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467340
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467345

Ceramalux ALTO Non-Cycling

Dimensional drawing



Product	D	L	C (max)
C250S50/ALTO NC HPS 1/12PK	2.25 inch	5.750 inch	9.75 inch

