



Switch Start Metal Halide Protected

MP1000/BU 6PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Voltage (Nom)	
Cap-Base	EX39 [Exclusionary Mogul Screw]	263 V	
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Mechanical and Housing	
Life to 50% Failures (Nom)	12,000 hour(s)	Bulb Finish	Clear
Light Technical		Bulb Material	Hard Glass
Color Code	635 [CCT of 3500K]	Bulb Shape	BT56
Color Designation	White (WH)	Net Weight (Piece)	0.001 kg
Chromaticity Coordinate X (Nom)	405	Approval and Application	
Chromaticity Coordinate Y (Nom)	390	Mercury (Hg) Content (Nom)	150 mg
Correlated Color Temperature (Nom)	3500 K	Product Data	
Luminous Efficacy (rated) (Nom)	107 lm/W	Order product name	MP1000/BU 6PK
Color rendering index (CRI)	65	Full product name	MP1000/BU 6PK
Operating and Electrical		Order code	928601179601
Lamp Current (Nom)	4.1 A	Material Nr. (12NC)	928601179601

Switch Start Metal Halide Protected

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281182
Numerator - Packs per outer box	6

EAN/UPC - Case	50046677281187
----------------	----------------

Dimensional drawing



Product	D	C (max)
MP1000/BU 6PK	7 inch	15.375 inch

