



MASTER LEDtube T8

MASTER LEDtube Starter EMP

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime ensure this tube masters every demanding application.

Warnings and Safety


- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.

Product data

General Information		Full product name	
Lighting Technology	LEDtube	Full product code	MASTER LEDtube Starter EMP
Operating and Electrical		Order code	871829172928000
Line Frequency	50 to 60 Hz	Material Nr. (12NC)	929000299902
Input Frequency	50 to 60 Hz	Numerator - Quantity Per Pack	1
Mechanical and Housing		EAN/UPC - Product/Case	8718291729280
Net Weight (Piece)	0.003 kg	Numerator - Packs per outer box	40
Product Data		EAN/UPC - Case	8718291729303
Order product name	MASTER LEDtube Starter EMP		

MASTER LEDtube T8

Dimensional drawing



Product	D1	D2	C1
MASTER LEDtube Starter EMP	3 mm	21.5 mm	34.5 mm

