



中国国家强制性产品认证证书

证书编号: 2017011002993099

发证日期: 2022年09月27日

有效期至: 2027年09月26日

认证委托人名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

产品生产者名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED 模块用交流电子控制装置(LED控制装置, 内装式, 控制端口调光, 恒流模式, $t_c: 85/90^{\circ}\text{C}$, $t_a: 55^{\circ}\text{C}$, 定温热保护: 130°C)
见附件. 220-240V ~ 50/60Hz

产品标准和技术要求 GB 17625.1-2012; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2017年08月10日

经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2017011002993099

Valid from: Sep.27,2022

Valid until: Sep.26,2027

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

PRODUCT MODEL(S)

A.C. Supplied Electronic Controlgear For LED Modules (Built-in, Controlled Port Dimming, Constant
Current Mode, tc:85/90°C, ta: 55°C, Temperature Declared Thermally Protected: 130°C)
See Appendix. 220-240V ~ 50/60Hz

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Aug.10,2017

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号 2017011002993099

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3089581

型号规格见下表:

序号	型号	输入规格	输出电流	输出电压	最大输出电压	输出功率	tc值
1	Xi LP 75W 0.2-0.7A S1 230V S240 sXt	220-240V~, 50/60Hz	0.2-0.7A	50-150Vdc	190Vdc	75W	85°C
2	Xi LP 75W 0.3-1.0A S1 230V S240 sXt	220-240V~, 50/60Hz	0.3-1.05A	35-108Vdc	140Vdc	75W	85°C
3	Xi LP 150W 0.2-0.7A S1 230V S240 sXt	220-240V~, 50/60Hz	0.2-0.7A	90-283Vdc	340Vdc	150W	90°C
4	Xi LP 150W 0.3-1.0A S1 230V S240 sXt	220-240V~, 50/60Hz	0.3-1.05A	70-214Vdc	260Vdc	150W	90°C
5	Xi LP 150W 0.5-1.5A S1 230V S240 sXt	220-240V~, 50/60Hz	0.5-1.5A	50-142Vdc	200Vdc	150W	90°C



中国质量认证中心

