



中国国家强制性产品认证证书

证书编号: 2017011002993094

委托人名称、地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者(制造商)名称、地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称、地址

台表科技(苏州)电子有限公司
江苏省吴江经济技术开发区甘泉东路 888 号

产品名称和系列、规格、型号

LED 模块用交流电子控制装置(LED 控制装置, 内装式, 控制端口调光, 恒流模式, $t_a: 55^{\circ}\text{C}$, $t_c: 85/90^{\circ}\text{C}$, 定温热保护: 130°C)

见附件。220-240V~ 50/60Hz

产品标准和技术要求

GB17625.1-2012; GB/T17743-2017; GB19510.1-2009; GB19510.14-2009

上述产品符合强制性产品认证实施规则 CNCA-C10-01:2014 的要求, 特发此证。

发证日期: 2019 年 07 月 05 日 有效期至: 2022 年 08 月 10 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2017 年 08 月 10 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



主 任:

陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2017011002993094

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE FACTORY

Taiwan Surface Mounting Technology (SuZhou) Co., Ltd.
No.888 GanQuan Dong Road Economic Technology Development Zone WuJiang

PRODUCT NAME, MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (Built-in, Controlled Port Dimming, Constant Current Mode, ta: 55°C, tc:85/90°C, Temperature Declared Thermally Protected: 130°C)

See Appendix. 220-240V~ 50/60Hz

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB17625.1-2012;GB/T17743-2017;GB19510.1-2009;GB19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C10-01:2014).

Valid from: Jul.05,2019

Valid until: Aug.10,2022

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Aug.10,2017

The certificate information is available through CNCA's website: www.cnca.gov.cn



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

变更结论 Modification Approval

证书编号 Certificate No. : 2017011002993094

申请编号 Application No. : A2019CCC1002-3200078

申请人(委托人) Applicant: 昕诺飞(中国)投资有限公司 / Signify (China) Investment Co., Ltd.

证书编号 Certificate No.(变更前 Original): 2017011002993094

变更产品名称: LED 模块用交流电子控制装置(LED 控制装置, 内装式, 控制端口调光, 恒流模式, ta: 55℃, tc:85/90℃, 定温热保护: 130℃)

Name of Product Modified: A.C. Supplied Electronic Controlgear For LED Modules (Built-in, Controlled Port Dimming, Constant Current Mode, ta: 55℃, tc:85/90℃, Temperature Declared Thermally Protected: 130℃)

变更情况 Situation of Modification (见下表 See table below) :

序号	项目 Item	变更前 Original	变更后 Present
1	EMC 标准换版	GB/T 17743-2007	GB/T 17743-2017
2	变更产品铭牌样式	见原报告	见本次变更报告: C-00201-19M-1120
3	变更报告中委托人和生产者名称	飞利浦照明(中国)投资有限公司	昕诺飞(中国)投资有限公司

现批准以上变更。

Above Modification is approved. The present will replace the original.

批准日期(Date): 2019年07月05日

第 1 页 / 共 1 页



主任:

陆楠



中国质量认证中心



中国国家强制性产品认证证书

附录

第 1 页 共 1 页

证书编号: 2017011002993094

纸 号: 2335153

型号	输出电流	输出电压	最大输出电压	输出功率	tc值
Xi LP 75W 0.2-0.7A S1 230V S240 sXt	0.2-0.7A	50-150Vdc	190Vdc	75W	85°C
Xi LP 75W 0.3-1.0A S1 230V S240 sXt	0.3-1.05A	35-108Vdc	140Vdc	75W	85°C
Xi LP 150W 0.2-0.7A S1 230V S240 sXt	0.2-0.7A	90-283Vdc	340Vdc	150W	90°C
Xi LP 150W 0.3-1.0A S1 230V S240 sXt	0.3-1.05A	70-214Vdc	260Vdc	150W	90°C
Xi LP 150W 0.5-1.5A S1 230V S240 sXt	0.5-1.5A	50-142Vdc	200Vdc	150W	90°C

输入: 220-240V~ 50/60Hz

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心