



中国国家强制性产品认证证书

证书编号: 2015011002809090

委托人名称、地址

昕诺飞(中国)投资有限公司

上海市闵行区田林路 888 弄 9 号楼

生产者(制造商)名称、地址

昕诺飞(中国)投资有限公司

上海市闵行区田林路 888 弄 9 号楼

生产企业名称、地址

产品名称和系列、规格、型号

LED 模块用交流电子控制装置(LED 控制装置, 内装式, 可调光, 恒

流模式, $t_c: 85/90^{\circ}\text{C}$, $t_a: 55^{\circ}\text{C}$, 定温热保护: 130°C)

见附件. 220-240V~ 50/60Hz

产品标准和技术要求

GB 17625.1-2012; GB/T 17743-2007; GB 19510.1-2009; GB
19510.14-2009

上述产品符合强制性产品认证实施规则 CNCA-C10-01:2014 的要求,
特发此证。

发证日期: 2020 年 09 月 02 日 有效期至: 2025 年 09 月 02 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2015 年 09 月 29 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

经中国合格评定国家认可委员会认可 CNAS C001-P



主任:

陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2015011002809090

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE FACTORY

PRODUCT NAME, MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (Built-in, Dimmable,
Constant Current Mode, tc:85/90°C, ta: 55°C, Temperature Declared Thermally
Protected: 130°C)

See Appendix. 220-240V~ 50/60Hz

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2012;GB/T 17743-2007;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO.CNCA-C10-01:2014).

Valid from: Sep.02,2020

Valid until: Sep.02,2025

The validity of the certificate is subject to positive result of the regular follow up
inspection by issuing certification body until the expiry date.

Date of original issued: Sep.29,2015

The certificate information is available through CNCA's website: www.cnca.gov.cn

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

<http://www.cqc.com.cn>

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666

Q 2683887



中国国家强制性产品认证证书

附 录

第 1 页 共 1 页

证书编号: 2015011002809090

纸 号: 2683887

型号	输出电流	输出电压	最大输出 电压	输出 功率	tc值
Xi LP 150W 0.2-0.7A S1 230V S240 sXt	0.2-0.7A	90-283Vdc	340Vdc	150W	90°C
Xi LP 150W 0.3-1.0A S1 230V S240 sXt	0.3-1.0A	70-214Vdc	260Vdc	150W	90°C
Xi LP 150W 0.5-1.5A S1 230V S240 sXt	0.5-1.5A	50-142Vdc	200Vdc	150W	90°C
Xi LP 150W 0.2-0.7A SN 230V S240 sXt	0.2-0.7A	90-283Vdc	340Vdc	150W	90°C
Xi LP 75W 0.2-0.7A S1 230V S240 sXt	0.2-0.7A	50-150Vdc	190Vdc	75W	85°C
Xi LP 75W 0.3-1.0A S1 230V S240 sXt	0.3-1.0A	35-108Vdc	140Vdc	75W	85°C
Xi LP 75W 0.2-0.7A SN 230V S240 sXt	0.2-0.7A	50-150Vdc	190Vdc	75W	85°C

输入: 220-240V~ 50/60Hz

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心