



MASTER Plastic LEDcandles & lusters

MASTER LEDcandle DT 6-40W E14 B38 CL_AP

LEDbulb, B38, 40 W, E14, 470 lm, 25000 hour(s)

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	E14		75 lm/W
Nominal lifetime	25,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	80
Lighting Technology	LEDbulb	LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	822-827 [tunable warm white]	Line Frequency	50 to 60 Hz
Luminous Flux	470 lm	Input Frequency	50 to 60 Hz
Color Designation	Warm White (WW)	Power Consumption	6 W
		Lamp Current (Nom)	35 mA

MASTER Plastic LEDcandles & lusters

Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	95 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	B38
Net Weight (Piece)	0.063 kg

Approval and Application

Suitable For Accent Lighting	No
------------------------------	----

Energy Consumption kWh/1000 h	6 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	MAS LEDcandle DT 6-40W E14 B38 CL_AP
Full product name	MASTER LEDcandle DT 6-40W E14 B38 CL_AP
Full product code	871869645352000
Order code	45352000
Material Nr. (12NC)	929001140408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696453520
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696453537

Dimensional drawing




Product	D	C
MAS LEDcandle DT 6-40W E14 B38 CL_AP	38 mm	113 mm

Photometric data



Light Distribution Diagram - MAS LEDcandle DT 6-40W E14 B38 CL_AP



Spectral Power Distribution Colour - MAS LEDcandle DT 6-40W E14 B38 CL_AP

MASTER Plastic LEDcandles & lusters

