



Classic LED spotMV

LEDClassic 4.6W GU10 830 60D 6pack

LEDspot, PAR16, 50 W, GU10, 3000 K, 410 lm, 15000 h, Glass

LEDspot, PAR16, 50 W, GU10, 3000 K, 410 lm, 15000 h, Glass, 89 lm/W

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	60 degree(s)
Luminous Flux	410 lm
Luminous Intensity (Nom)	450 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	89 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	4.6 W
Lamp Current (Nom)	39 mA
Wattage Equivalent	50 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Overall length	54 mm
Overall width	50 mm
Overall height	54 mm
Dimensions (Height x Width x Depth)	54 x 50 x 54 mm
Bulb Shape	PAR16
Net Weight (Piece)	0.050 kg
Approval and Application	
Suitable For Accent Lighting	Yes

Classic LED spotMV

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	LEDClassic 4.6W GU10 830 60D 6pack
--------------------	------------------------------------



Full product name	LEDClassic 4.6W GU10 830 60D 6pack
Full product code	871869681901200
Order code	929001287698
Material Nr. (12NC)	929001287698
Numerator - Quantity Per Pack	6
EAN/UPC - Product/Case	8718696819012
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696819029

Dimensional drawing



Product	D	C
LEDClassic 4.6W GU10 830 60D 6pack	50 mm	54 mm

Photometric data




Spectral Power Distribution Colour - LEDClassic 4.6W GU10 830 60D 6pack

Accent Lighting Spots - LEDClassic 4.6W GU10 830 60D 6pack

Classic LED spotMV

Photometric data



Light Distribution Diagram - LEDClassic 4.6W GU10 830 60D 6pack

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDClassic 4.6W GU10 830 60D 6pack

