



# Classic LED spotMV

## LEDClassic 4.6W GU10 840 60D 2pack

LEDspot, PAR16, 50 W, GU10, 4000 K, 430 lm, 15000 hour(s), Glass

LEDspot, PAR16, 50 W, GU10, 4000 K, 430 lm, 15000 hour(s), Glass, 93 lm/W

### Product data

General Information		Wattage Equivalent	
Cap-Base	GU10		50 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LEDspot	Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	60 degree(s)		
Luminous Flux	430 lm	Controls and Dimming	
Luminous Intensity (Nom)	450 cd	Dimmable	No
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	93 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Overall length	54 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Overall width	50 mm
		Overall height	54 mm
		Dimensions (Height x Width x Depth)	54 x 50 x 54 mm
Operating and Electrical		Bulb Shape	PAR16
Input Frequency	50 to 60 Hz	Net Weight (Piece)	0.050 kg
Power Consumption	4.6 W		
Lamp Current (Nom)	39 mA		

# Classic LED spotMV

## Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

## Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

## Product Data

Order product name	LEDClassic 4.6W GU10 840 60D 2pack
--------------------	------------------------------------



Full product name	LEDClassic 4.6W GU10 840 60D 2pack
Full product code	871869969111000
Order code	929001287792
Material Nr. (12NC)	929001287792
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8718699691110
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699691127

## Dimensional drawing



Product	D	C
LEDClassic 4.6W GU10 840 60D 2pack	50 mm	54 mm

## Photometric data




Accent Lighting Spots - LEDClassic 4.6W GU10 840 60D 2pack

Light Distribution Diagram - LEDClassic 4.6W GU10 840 60D 2pack

# Classic LED spotMV

## Photometric data




Spectral Power Distribution Colour - LEDClassic 4.6W GU10 840 60D 2pack

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDClassic 4.6W GU10 840 60D 2pack

