



Party Spot

13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF

LEDspot, PAR38, E26, 10950 hour(s), Glass

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Product data

General Information	
Cap-Base	E26
Nominal lifetime	10,950 hour(s)
Switching Cycle	10,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LEDspot
Light Technical	
Color Code	Green
Color Designation	Green
Color Consistency	<6
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	13.5 W
Lamp Current (Nom)	165 mA
Starting Time (Nom)	0.5 s

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
UL Type	Yes
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Overall length	132 mm
Overall width	122 mm
Overall height	132 mm
Dimensions (Height x Width x Depth)	132 x 122 x 132 mm
Bulb Shape	PAR38
UL Wet/ damp/ dry location	Wet location

Party Spot

Net Weight (Piece)	0.350 kg
--------------------	----------

Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	N/A
LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C


Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data



Order product name	13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF
Full product name	13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF
Order code	929001306763
Material Nr. (12NC)	929001306763
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568283
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677568288

Dimensional drawing



Product	D	C
13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF	122 mm	132 mm

Photometric data





Light Distribution Diagram - 13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF

Accent Lighting Spots - 13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF

Party Spot

Lifetime



Lumen Maintenance Diagram - 13.5PAR38/PER/GREEN/G/E26/ND/ULW
3/IPF

Life Expectancy Diagram

