



# Party Spot

13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

LEDspot, PAR38, E26, 10950 hour(s), Glass

LEDspot, PAR38, E26, 10950 hour(s), Glass

## Product data

General Information		UL Type	
Cap-Base	E26	UL Type	Yes
Nominal lifetime	10,950 hour(s)	<b>Temperature</b>	
Switching Cycle	10,000	T-Case Maximum (Nom)	65 °C
Rated Lifetime (Hours)	10,950 hour(s)	<b>Controls and Dimming</b>	
Lighting Technology	LEDspot	Dimmable	No
<b>Light Technical</b>		<b>Mechanical and Housing</b>	
Color Code	Red	Bulb Finish	Frosted
Color Designation	Red	Bulb Material	Glass
Color Consistency	<6	Overall length	132 mm
Color rendering index (CRI)	-	Overall width	122 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Overall height	132 mm
<b>Operating and Electrical</b>		Dimensions (Height x Width x Depth)	132 x 122 x 132 mm
Line Frequency	60 Hz	Bulb Shape	PAR38
Input Frequency	60 Hz	UL Wet/ damp/ dry location	Wet location
Power Consumption	13.5 W	Net Weight (Piece)	0.350 kg
Lamp Current (Nom)	165 mA	<b>Approval and Application</b>	
Starting Time (Nom)	0.5 s	Suitable For Accent Lighting	Yes
Warm-up time to 60% light	0.5 s	EU RoHS compliant	Yes
Power Factor (Fraction)	0.5	EyeComfort	Yes
Voltage (Nom)	120 V		

## Party Spot

T20 compliant	N/A
LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C

### Application Conditions


can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

### Product Data

Order product name	13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF
--------------------	--------------------------------------



Full product name	13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF
Order code	929001306863
Material Nr. (12NC)	929001306863
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568290
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677568295

## Dimensional drawing



Product	D	C
13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF	122 mm	132 mm

## Photometric data





Accent Lighting Spots - 13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

Light Distribution Diagram - 13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

# Party Spot

## Lifetime



Lumen Maintenance Diagram - 13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

Life Expectancy Diagram

