




# CorePro LED tube Mains T5

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	600 mm
Bulb Shape	T5
Net Weight (Piece)	0.070 kg
Approval and Application	
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EU RoHS compliant	Yes



Ambient temperature range	-20 °C to 45 °C
Product Data	
Order product name	CorePro LEDtube 600mm 8W830 G5 I APR
Full product name	CorePro LEDtube 600mm 8W830 G5 I APR
Full product code	871869673196300
Order code	929001380608
Material Nr. (12NC)	929001380608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696731963
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696731970

## Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W830 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm

## Photometric data




General uniform lighting - CorePro LEDtube 600mm 8W830 G5 I APR

Spectral Power Distribution Colour - CorePro LEDtube 600mm 8W830 G5 I APR

General uniform lighting - CorePro LEDtube 600mm 8W830 G5 I APR


# CorePro LED tube Mains T5

## Photometric data




Light Distribution Diagram - CorePro LEDtube 600mm 8W830 G5 I APR


## Lifetime




ESSENTIAL LEDtube 8-16W G5 830-865 APR



ESSENTIAL LEDtube 8-16W G5 830-865 APR




ESSENTIAL LEDtube 8-16W G5 830-865 APR



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W830 G5 I APR

## CorePro LED tube Mains T5

### Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W830 G5 I APR

